
ACR Liquid Line Filter/Drier Cutaway



Model: 373-601

DAC Worldwide's ACR Liquid Line Filter/Drier Cutaway (373-601) is a carefully-crafted, sectioned example of a commonly-encountered liquid line filter/drier. Liquid line filter/driers are designed to protect refrigeration system components from the negative effects of entrained water, formed acids and debris. These simplistic protective devices act as guardians for expensive system compressors, evaporators, and metering devices.

This economical, sectioned example showcases the device's operating principle, internal components, and related installation concerns. Multiple cutaways unveil all internal components, which enhances classroom training in HVAC system design, maintenance, troubleshooting, and preventive/predictive maintenance.

The full-size, fully-detailed example gives learners a first-hand view into a component that is found in various applications worldwide. This professionally-crafted component sample will enhance any training activity relating to commercial and industrial air conditioning and refrigeration systems.

Take Training to the Next Level with Hands-On Cutaway Industrial Components

This ACR Liquid Line Filter/Drier Cutaway provides a full cutaway view of a liquid line filter/drier that exposes the complete internal components and operating principles. Color coding, flow arrows, and numbered call-outs combine to make the device more informative to the inquiring student and more useful to the instructor. The device can be used independently using an optional tabletop mounting foot, or combined with similar devices on optional display and storage frame assemblies.

Economically mounted on a modular display panel, this sample panel can be combined with a variety of optional benchtop display fixtures and storage structures possess the ability to be removed from the baseplate for convenient classroom use. All of the cutaway's components are also visible and have been retained, enhancing students' visual learning. This professionally-crafted teaching aid will support instructor-led training and independent student self-discovery in a variety of vocational and academic air conditioning and refrigeration programs.

Finally, the equipment used within the cutaway is cleaned, primed and painted using a high-endurance urethane coating, providing durability to stand up to frequent use. In addition, all of the component parts are color coded to enhance the learning process.

Expand Training with Additional HVAC Model Options

The ACR Liquid Line Filter/Drier Cutaway is only one of DAC Worldwide's expansive HVAC training cutaways, which includes a Heat Pump Reversing Valve Cutaway (373-505), and ACR Magnetic Check Valve Cutaway (373-510), a Condenser Pressure Control Valve Cutaway (KVR) (373-519), a Schrader Service Valve Cutaway (373-529), and more!

FEATURES & SPECIFICATIONS

Important Product Note: Photographs are representative and for reference only. Product appearance and dimensions may vary based upon component manufacturer and availability. Any product dimensions given, such as size and weight, are approximate and for directional use only. For the most accurate shipping dimensions and weights, please contact the manufacturer.

- 13-gauge formed-steel mounting panel with provision for mounting on optional tabletop supports or larger group display structures
- Sectioning of actual new commercial components (makes and models by well-known manufacturers are chosen for industrial and commercial relevancy)
- All primary internal components shown including: blended desiccant core, leaf spring stabilizer, fiberglass pad filter, and outlet safety screen
- Customized component U-type support saddle and mounting straps
- Precision-painting of cutaway surfaces increasing definition and 3-dimensionality
- Laser-cut numbered call-outs, flow arrows, and designators showcasing key component features and flow pattern
- Packaging for shipment via parcel service or courier

PRODUCT DIMENSIONS DISCLAIMER: Product Dimensions are approximate. Shipping Dimensions and Weights are for directional use only and may change based on manufacturer variables. For the most accurate Shipping Dimensions and Weights, please contact the manufacturer.

• Product Dimensions

(L x W x H) 9in x 9in x 5.5in (225 x 225 x 140 mm)

• Shipping Dimensions

(L x W x H) 12in x 12in x 12in (300 x 300 x 300 mm)

OPTIONS

• Recommended 373-002 Tabletop Support Frame

- #373-001 Tabletop Support Foot
- #373-002E Tabletop Support Frame Assembly, Extended

Address

DAC Worldwide 601 Heron Drive Swedesboro, NJ 08085

Contacts

email: contact@dacworldwide.com

phone: (800) 662 5877