Tank Mixing Eductor Cutaway



Model: 273-736

DAC Worldwide's Tank Mixing Eductor Cutaway (273-736) allows for effective and convenient classroom training in the design, operating principles, and construction geometry of an industrial tank mixing eductor. The complete device is sectioned exposing all primary features including the motive nozzle inlet, the suction mixing inlet, mixing venturi area, and the discharge. The complete geometry of this fundamental piece of equipment is exposed facilitating a better understanding of its operating principles and purpose in industrial applications.

Tank mixing eductors are used to agitate liquid, dissolve powdered solids in liquid, and mix two or more liquids within a tank without the use of baffles or moving parts inside the tank. These units take the place of mechanical agitators.

The cutaway is mounted on a 13-gauge, formed-steel, powder-coated mounting stand with clip-type attachment brackets. It can also be mounted on related DAC Worldwide bench, workstation, storage rack, and display products.

FEATURES & SPECIFICATIONS

Important Product Note: Photographs are representative and for reference only. Product appearance and dimensions may vary based upon component manufacturer and availability. Any product dimensions given, such as size and weight, are approximate and for directional use only. For the most accurate shipping dimensions and weights, please contact the manufacturer.

- Sectioning of an actual bronze or steel device; common valve brands and models are chosen for industrial relevancy
- Cleaning and sealing using a clear coating
- Complete sectioning, unveiling the complete interior geometry of the device
- 13-Gauge, formed-steel, power coated, mounting stand with clip-type attachment brackets
- Provision for mounting on related DAC bench, workstation, and storage rack and display products

PRODUCT DIMENSIONS

DISCLAIMER: Product Dimensions are approximate. Shipping Dimensions and Weights are for directional use only and may change based on manufacturer variables. For the most accurate Shipping Dimensions and Weights, please contact the manufacturer.

• 12.25-in. L x 8.5-in. W x 8.5-in. H (311x 215 x 215 mm)

OPTIONS

• Recommended #902V - Mobile Display Stand

Address

DAC Worldwide 601 Heron Drive Swedesboro, NJ 08085

Contacts

email: contact@dacworldwide.com phone: (800) 662 5877